

■バックアップ時間の目安■

※周囲温度25℃・バッテリー初期状態の場合。本バックアップ時間はあくまでも参考値となります。バッテリーの寿命および外部環境（温度など）によって変わります。

●常時インバータ給電方式 (BU/BAシリーズ)

時間単位：(分)

型式/負荷容量	20W	50W	100W	200W	300W	400W	500W	600W	700W	800W	900W	1000W	1100W	1200W	1300W	1400W	1500W	1600W	1700W	1800W	1900W	2000W	2100W	2200W	2300W	2400W	2500W	2600W	2700W	2800W	2900W	3000W	3100W	3200W	3300W	3400W	3500W
BU500R2RWL	660	480	320	200	140	106	83	68	57	50	44	39	34	31	27.7	25	23	21	19	18	17	16	15	14	13	12	11.3	10.6	10	9.3	8.6	8	7.6	7.3	7	6	5
BU300R2RWL	450	260	165	93	63	45	34.0	28	22	19	16	15	13	11	10	9	8.2	7.5	6.7	6	5.6	5.2	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
BU200R2RWL	360	190	110	60	39	27	20	16	13	12	10.6	9.5	8	7	6	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
BU100R2RWL	140	80	48	24	15	11	9	6	4.5	3.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU3002SW	360	250	170	92	58	46	36	30	24	20	17	15	13.3	12	11	10	9	8	7.5	7	6.2	5.5	5	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU3002SW+BUM300S×1	1030	920	570	340	220	175	139	115	97	85	72	62	55	49	46	43	40	37	34	31	28.3	26	24	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU1002SW	180	120	60	35	20	15	10	7	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU1002SW+BUM100S×1	720	620	240	120	80	60	48	40	30	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU100RE	150	110	72	32	20	15	11	8.5	7	6	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU100RE+BUM100RE×1	680	470	280	137	86	62	46	36	29	25	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU100RE+BUM100RE×2	1210	840	480	240	160	115	89	72	58	48	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU100RE+BUM100RE×3	1740	1190	720	370	250	178	136	110	89	75	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
BU60RE	115	75	42	19	12	8	6(480W)	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU300RW	320	220	150	80	52	40	31	26	21	18	16	14	12	11	10	9	8	7	6.5	6	5.6	5.3	4.9	4.6	4.3	4	-	-	-	-	-	-	-	-	-		
BU300RW+BUM300R×1	900	800	500	240	200	150	120	100	85	75	63	55	49	44	39	35	32	30	28	26	24	23	21	20	19	18	-	-	-	-	-	-	-	-	-	-	
BU200RW	320	220	150	80	52	40	31	26	21	18	16	14	12	11	10	9	8	7	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU200RW+BUM300R×1	900	800	500	240	200	150	120	100	85	75	63	55	49	44	39	35	32	30	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU100RW	250	150	85	36	23	18	13	10	8.3	7	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU100RW+BUM100R	860	520	320	170	100	75	56	44	36	31	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU75RW	250	150	85	36	23	18	13	10	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU75RW+BUM100R	860	520	320	170	100	75	56	44	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU150R	460	241	126	65	41	29	22	18	15	13	10	8	7.2	6.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU150R+BUM150RA×1	1660	750	438	235	153	107	82.7	67	55	47	41	36	32	29	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU150R+BUM150RA×2	2250	1100	700	380	260	186	149	125	104	90	77	68	62	58	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU150R+BUM150RA×3	3550	1680	1050	575	370	273	213	175	150	132	114	100	90	82	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU150R+BUM150RA×4	4500	2500	1300	720	482	354	282	235	195	167	146	130	118	108	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU150R+BUM150RA×5	5550	3200	1580	850	580	425	341	285	235	200	178	160	144	132	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU150R+BUM150RA×6	6500	3700	1680	1030	710	517	413	345	287	245	214	190	172	158	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU150SW	210	150	70	37	23	17	12	10	8.3	7	5.3	4.2	4(1050W)	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU150SW+BUM150S×1	740	440	260	140	90	65	51	43	34	28	24	21	20(1050W)	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU100SW	180	120	60	35	20	15	10	7	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU100SW+BUM100S×1	720	420	240	120	80	60	48	40	30	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU75SW	120	75	40	20	12	7	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU50SW	120	75	40	20	12	8(350W)	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BU100RS	200	109	56	23	14	9	7.2	6	5	4	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BA100R	200	109	56	23	14	9	7.2	6	5	4	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BA100T	200	109	56	23	14	9	7.2	6	5	4	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BA75T	200	109	56	23	14	9	7.2	6	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	

●ラインインタラクティブ方式 (BL/BNシリーズ)

時間単位：(分)

型式/負荷容量	20W	50W	100W	200W	300W	400W	500W	600W	700W	800W	900W	1000W	1100W	1200W	1300W	1400W	1500W	1600W	1700W	1800W	1900W	2000W	2100W	2200W	2300W	2400W	2500W	2600W	2700W								
BL100T	160	90	54	30	20	15	12	10	7.5	6	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-		
BL75T	120	68	40	21	15	10.5	8	6.4	5(680W)	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-		
BL50T	80	45	26	14	10.5	7	6(450W)	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-		
BN300R	600	300	170	90	55	40	31	26	21.4	18	15.2	13	11.5	10.2	9.1	8.2	7.2	6.4	5.6	5	4.7	4.5	3.8	3.2	2.7	2.6	2.6	2.5	2.5	-	-	-	-	-			
BN150R	480	215	120	56	35	25	19.6	16	13	11	9.3	8	7	6.2	5	4.5(1350W)	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-		
BN75R	250	100	55	24	15.5	10.5	7.6	5.8	4(680W)	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BN150XR	220	130	70	37	20	15	11.3	9	6.9	5.5	4.6	4	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-		
BN300T	900	460	250	125	81.5	57	44	36	29.6	25	21	18	15.8	14	12.4	11	10.2	9.5	8.7	8	7.5	7	6.6	6.2	5.8	5.4	5.1	4.8	4.5	-	-	-	-	-	-		
BN220T	900	460	250	125	81.5	57	44	36	29.6	25	21	18	15.8	14	12.4	11	10.2	9.5	8.7	8	7.4	7(1980W)	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
BN150T	480	215	120	56	35	25	19	16	13	11	9.3	8	7	6.2	5	4.5(1350W)	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
BN100T	480	215	120	56	35	25	19	16	13	11	9																										

■バックアップ時間の目安（生産終了機種）■

※周囲温度20℃・バッテリー初期状態の場合。本バックアップ時間はあくまでも参考値となります。バッテリーの寿命および外部環境（温度など）によって変わります。

●常時インバータ給電方式

時間単位：（分）

型式／負荷容量	20W	50W	100W	200W	300W	400W	500W	700W	1000W	1400W
BU1006F	180	90	60	25	18	12	9	5	-	-
BU1006F+M B 1006Fx1	360	240	120	70	40	30	24	15	-	-
BU1006F+M B 1006Fx2	720	360	240	100	70	55	37	25	-	-
BU606F	150	90	40	19	12	5(420W)		-	-	-
BU2006 II	---	150	100	70	50	40	28	20	14	5
BU2006 II + M B 2006 II x1	480	300	210	150	100	80	70	50	30	20
BU2006 II + M B 2006 II x2	720	600	360	210	150	120	100	70	60	33
BU1006 II	180	80	50	23	18	10	8	5	-	-
BU1006 II + M B 1006 II x1	300	180	100	55	33	28	23	14	-	-
BU606 II	120	60	30	18	10	5(420W)		-	-	-
BU200XR2	420	240	120	80	50	35	28	17	10	5
BU200XR2+MB200XR2x1	780	480	360	180	100	80	65	40	30	17
BU200XR2+MB200XR2x2	1320	900	420	270	180	120	100	70	50	32
BU100XR2	180	120	60	35	20	15	10	5	-	-
BU100XR2+MB100XR2	720	420	240	120	80	60	50	30	-	-
BU100XS	180	120	60	35	20	15	10	5	-	-
BU100XS+MB100XSU	720	420	240	120	80	60	50	30	-	-
BU70XS	120	75	40	20	12	7	5(490W)	-	-	-
BU50XS	120	75	40	20	12	8(350W)	-	-	-	-

型式／負荷容量	20W	50W	100W	200W	300W	400W	600W	800W
BH100PCW (*3)	100	70	45	25	14	10	5	4(700W)
BH100PCW+BHM100PCx1	210	140	95	50	35	25	15	12(700W)
BH100PCW+BHM100PCx2	320	220	140	80	55	40	25	20(700W)
BH100PCW+BHM100PCx3	430	300	190	110	75	55	35	30(700W)
BH100PCW+BHM100PCx4	550	380	260	140	95	70	45	40(700W)
BH60PCW (*3)	65	40	23	13	8	5.1	5(420W)	-

(*3)BH60PCW、BH100PCW 共にバッテリーユニットが標準添付されており、基本構成は2ユニット構成です。

●ラインインラクティブ方式

時間単位：（分）

型式／負荷容量	20W	50W	100W	200W	300W	400W	600W	800W	1000W	1200W	1400W	1600W	1800W	2000W	2300W	2700W
BN300S	900	600	320	150	88	64	38	25	18	15	12	10	8.4	7.5	6	5
BN220S	900	600	320	150	88	64	38	25	18	15	12	10	8.4	7(1980W)	-	-
BN150S	620	290	140	60	35	24	13	9	7	5.5	5(1350W)	-	-	-	-	-
BN100S	620	290	140	60	35	24	13	9	7.9(900W)	-	-	-	-	-	-	-
BN75S	230	109	49	21	12	8.2	4.6	3.5(680W)	-	-	-	-	-	-	-	-
BN50S	230	109	49	21	12	8.2	5.5(450W)	-	-	-	-	-	-	-	-	-

型式／負荷容量	20W	50W	100W	200W	300W	400W	500W	700W	1000W
BN140XS	360	180	100	50	32	21	16	10	5(940W)
BN100XS	240	120	60	35	21	15	11	5(670W)	-
BN75XS	150	80	40	20	12	7	5	-	-
BN50XS	150	80	40	20	12	8(335W)	-	-	-

●常時商用給電方式

時間単位：（分）

型式／負荷容量	20W	50W	100W	200W	300W	400W	500W	700W
BU1004X3(*2)	60	60	55	25	20	12	8	5
BU504X4/BU504XL4(*2)	60	60	30	14	8	5	-	-
BU251X(*1)	70	30	10	5(165W)	-	-	-	-
BX75XS2(*1)	90	90	50	22	12	7	5(450W)	-
BX50XFV/BX50XFS(*1)	90	50	20	6	3.5	-	-	-
BX35XFV/BX35XFS(*1)	90	50	20	6	5(210W)	-	-	-
BX25XT(*1)	40	22	8	3.5(168W)	-	-	-	-
BX50LS(*1)	90	50	20	6	3	-	-	-
BZ50LT(*1)	90	45	19	6	3	-	-	-
BZ50T(*1)	90	45	19	6	3	-	-	-
BZ35T(*1)	74	28	10	3	-	-	-	-

(*1)最大バックアップ時間の制限があります。90分以上のバックアップはできません。

(*2)最大バックアップ時間の制限があります。60分以上のバックアップはできません。